GENERON

Oxygen Generating Systems Oxygen PSA - OS-30-68



Typical Applications


- Health care
- Fish farming
- Sewage treatment
- Glass industry
- Food industries
- Sewage treatment
- Pulp and paper industry
- · Welding, melting, brazing
- Manufacturing batteries
- · Chemical oxidation

♦ Advantages of GENERON® OXYSWING PSA

- Low operating pressures
- No hazardous storage or connections
- Low gas generating costs
- · Low operating cost
- Fully automatic unattended operation
- Two million plus cycle valves
- Easy to install and maintain
- Low dBA levels

GENERON® Oxygen PSA Generators separates oxygen (O2) from compressed air utilizing pressure swing adsorption technology. Compressed air, which consists of approximately 21% oxygen and 78% nitrogen, is passed through a bed of zeolite molecular sieve (ZMS). The sieve preferentially adsorbs N2 and moisture over O2 allowing the O2 to pass through as a product gas at pressure. While one of the towers is in the adsorption phase the other tower is regenerated by de-pressurizing, at which time the sieve releases the adsorbed gases to the atmosphere, and the cycle is then repeated.

A solid state programmable controller operates the process valves on an alternating cycle, with built-in logic for automatic stop/start. Oxygen flow and purity remain constant regardless of the peak usage demands. Under normal operating conditions and with correct maintenance the zeolite molecular



Oxygen Generating Systems

OS-30-68 Technical Data - US Standards

Oxygen Production Flow						
(Nm³/h) / (Scfh)			Length	Width	Height	Weight
90 vol.%	93 vol.%	95 vol.%	(mm) / (inch)	(mm) / (inch)	(mm) / (inch)	(kg) / (lbs)
38.9 / 1481	35.6 / 1354	30.9 / 1176	2083 / 82	1727 / 68	2616 / 103	3134 / 6909

^{*}All performance flows are +/- 4%. All flows are shown at 68° F / 20°c.

♦ Standard Components

- ASME adsorber vessels
- Pneumatic/electric valves (two million cycle life)
- Piping, gauges, and instrumentation
- · Safety valve
- Oxygen pressure and flow regulators
- PLC control system (Allen Bradley)
- Steel wrap around skid mounted
- Exhaust silencing muffler
- Sound level < 90 dBA

GENERON

16250 Tomball Parkway Houston, Texas 77086 O +1 713 937 5200 F +1 713 932 5250 **GENERON**

Options

- Oxygen analyzer (with calibration kit)
- · Product flow meter
- · Inlet filtration package
- · Post filtration package
- Auto shut down/startup mode (with manual bypass valve capability)
- · Auto standby mode
- Off specification circuit
- HMI Display Screen: displays inlet pressure, outlet pressure, system run status, O2 concentriation
- CFV activated carbon filter vessel

Special Options

- Master controller: PLC (Allen Bradley) driven for multiple unit operation
- Enhanced PLC with telemetry
- Enhanced HMI: Monitor Package (displays feed air, nitrogen product pressures, oxygen concentration, and product flow)
- Compressed air buffer tank
- Oxygen buffer tank
- Product booster compressor
- · Dew point analyzer
- Tanks & generator on a common skid
- Custom engineered packages

